

Technical Specification

Drying cabinet for respiratory masks

For drying respirator masks and respirator components.



Drying cabinet 4 (fig. similar)

Made by



Drying cabinet as table-top model
with 2, 4 or 6 baskets for accommodating 12, 24 or 36 respirator masks or parts of breathing apparatus. Equipped with a drip pan for collecting the remaining liquid. Inner and outer housing made of stainless steel with insulated drying chamber.

Drying cabinet as stand model
with 8 or 10 baskets for 72 or 90 respirator masks or parts of breathing apparatus. Due to the larger basket spacing, the masks can be placed upright in the baskets.

- Heating with radial fan
- Integrated safety thermostat
- Timer
- Clean dry air through suction filter
- Removable baskets
- Wired ready to plug in
- Height-adjustable feet made of stainless steel
- Fixed drying temperature of max. 50°C, therefore overheating and damage to the masks is avoided



Drying cabinet 10 SM
(fig. similar)

TECHNICAL DATA

Model	MTS 2	MTS 4	MTS 6	MTS 8 SM	MTS 10 SM
Dimensions (W x D x H) in mm	770 x 532 x 468	770 x 532 x 818	770 x 532 x 1168	770 x 607 x 2050	770 x 607 x 2330
Weight approx. in kg	40	56	85	180	125
No. of baskets	2	4	6	8	10
Mask capacity	12	24	36	72	90
Rated current (KW)	1,1	2,3	2,3	4,2	4,2
Power connection (V/A)	230/16	230/16	230/16	400/3x16	400/3x16
External pressure drop (Pa)	freely blowing out	freely blowing out	freely blowing out	150	150
Volume flow (m3/h)	90	140	140	435	400
Exhaust air spigot (inner diameter)	-	150*	150*	200	200

* possible at extra charge

ORDER INFORMATION

Drying cabinet for respiratory masks 2	6573050
Drying cabinet for respiratory masks 4	6573051
Drying cabinet for respiratory masks 6	6573052
Drying cabinet for respiratory masks 8	6573053
Drying cabinet for respiratory masks 10	6573054

ACCESSORIES AND SPECIAL EQUIPMENT

Push-in basket	530 x 476 x 90	
Hole container with lid	220 x 220 x 80	
Hole container with upper part	448 x 452 x 20	
Hole container with bottom part	445 x 445 x 40	
Perforated plate container LBD22	With lid	6566497
Pass-through door	Extra charge for 2nd door, e.g. for black, white separation	

CORPORATE HEADQUARTERS

Drägerwerk AG & Co. KGaA
Moislinger Allee 53-55
23558 Lübeck, Germany
www.draeger.com

Manufacturer

Winterhoff Edelstahl GmbH
Bremer Weg 190
29223 Celle
Germany

REGION DACH

Dräger Safety AG & Co. KGaA
Revalstraße 1
23560 Lübeck
Tel +49 451 882 0
Fax +49 451 882 2080
info@draeger.com

REGION MIDDLE EAST, AFRICA

Dräger Safety AG & Co. KGaA
Branch Office
P.O. Box 505108
Dubai, United Arab Emirates
Tel +971 4 4294 600
Fax +971 4 4294 699
contactuae@draeger.com

REGION CENTRAL AND SOUTH AMERICA

Dräger Panama S. de R.L.
Complejo Business Park
V tower, 10th floor
Tel +507 377 9100
Fax + 507 377 9130
contactcsa@draeger.com

REGION ASIA PACIFIC

Draeger Safety Asia Pte Ltd
25 International Business Park
#04-20/21 German Centre
Singapore 609916
Tel +65 6308 9400
Fax +65 6308 9401
asia.pacific@draeger.com